

The System



The HSV-2000 system comprises an HSV-2001/2002 Controller, an HSV-800 Laser Unit and a rugged, compact HSV-700 Sensor Head. The Laser Unit houses the interferometer and the low power laser.

The Sensor Head is available in either fixed or variable focus versions. The fixed focus head has an extra long depth of field and is recommended for measuring large displacements. One Laser Unit connects to the HSV Controller for the single channel (HSV-2001) version and two units for dual or differential measurements (HSV-2002).

The HSV-2001 incorporates a 6 range displacement decoder with 0.32 mm resolution and a maximum displacement of ± 82 mm. In addition there is a single range velocity decoder for vibration frequencies up to 50 kHz with a fixed scaling of 5 m/s/V. Applications such as valve train testing require differential measurements. One laser beam is targeted onto the valve while the other is directed onto the cylinder. The HSV-2002 provides separate velocity outputs for channel A, channel B and the difference A-B. Displacement information is available for channel A and the difference. The desired velocity and displacement output signals are selected by a rotary switch on the front panel.

Both controllers feature a large bar-graph display showing the amount of return signal from the test object. The actual displacement range is selected by push buttons and indicated on the LCD display. An input signal from the device being tested (e.g. a cam shaft position) can trigger the displacement measurement through a front panel connector. Please find detailed technical data of the system on pages 4 and 6.

For data acquisition, an FFT analyzer, digital oscilloscope or A/D board is connected to the analog HSV signal outputs. In addition, the Polytec displacement PC board (fringe counter) may be connected to the rear panel digital interface. Please check the VibSoft-FC data sheet for more information.

To learn more about laser Doppler vibrometry, please visit www.polytec.com/usa/vib-university.

Accessories

AK-800 Beam Steering Unit

The AK-800 Beam Steering Unit was designed for precise positioning of the measuring laser spot on the test object. For spot positioning, the beam exit tube may be tilted and/or rotated. The AK-800 can only be used with the fixed focus version (ff) of the HSV-700 Sensor Head.

Focus adjustment is achieved by moving the HSV-700 Sensor Head mounted on a common traverse stage with the AK-800. The AK-800 is oil-tight and was engineered specifically for valve train measurements.

CLV-A-Micro Microscope Adapter

This adaptor enables interfacing the HSV-700 Sensor Head to our standard microscope adapters MSV-050 and MSV-100 to enable high speed measurements through a microscope.



Polytec GmbH (Germany)
 Polytec-Platz 1-7
 76337 Waldbronn
 Tel. +49 (0) 7243 604-0
 Fax +49 (0) 7243 69944
 info@polytec.de

Polytec-PI, S.A. (France)
 32 rue Délizy
 93694 Pantin
 Tel. +33 (0) 1 48 10 39 34
 Fax +33 (0) 1 48 10 09 66
 info@polytec-pi.fr

Lambda Photometrics Ltd. (Great Britain)
 Lambda House, Batford Mill
 Harpenden, Herts AL5 5BZ
 Tel. +44 (0) 1582 764334
 Fax +44 (0) 1582 712084
 info@lambdaphoto.co.uk


Polytec KK (Japan)
 Hakusan High Tech Park
 1-18-2 Hakusan, Midori-ku
 Yokohama-shi, 226-0006
 Kanagawa-ken
 Tel. +81 (0) 45 938-4960
 Fax +81 (0) 45 938-4961
 info@polytec.co.jp

Polytec, Inc. (USA)
 North American Headquarters
 1342 Bell Avenue, Suite 3-A
 Tustin, CA 92780
 Tel. +1 714 850 1835
 Fax +1 714 850 1831
 info@polytec.com

Midwest Office
 3915 Research Park Dr.,
 #A12
 Ann Arbor, MI 48108
 Tel. +1 734 662 4900
 Fax +1 734 662 4451

East Coast Office
 16 Albert Street
 Auburn, MA 01501
 Tel. +1 508 832 0501
 Fax +1 508 832 4667

Range Diagram



For general specifications and applications of the HSV-2000 High Speed Vibrometer please contact your local Polytec sales engineer or visit our website at www.polytec.com/usa/highspeed.



Laser Radiation
 Avoid exposure to beam
 Class 3B Laser Product
 According to IEC/EN 60825-1 (2001)
 Complies with 21 CFR 1040.10 and 1040.11
 except for deviations pursuant to
 Laser Notice no. 50, dated 26 July 2001
 P ≤ 50 mW/cw, λ = 620-700 nm



HSV-2000 High Speed Vibrometer

Measurement of Vibration Velocity and Displacement at High Speeds



**Non-contact
Single point or differential
Velocities up to ± 30 m/s**


High Speed Capability



The HSV-2000 series High Speed Vibrometer measures single or dual points plus differential vibration velocity and displacement at high speeds up to 30 m/s. This system is widely used by Formula1 engineers for the development of high performance valve trains for racing engines.

Vibration velocities up to 20 m/s can be handled with Polytec's standard line of Laser Doppler Vibrometers (LDVs). High performance applications require significantly increased speed capabilities.

The HSV has been designed to extend the maximum operating velocity by 50 % to 30 m/s specifically to meet applications such as valve train testing on motor sports engines, high power transducers, special drilling machines, impact testing and fatigue testing of aerospace components.



Key Features

- Velocity and displacement measurement for vibration speeds up to 30 m/s
- Single or dual points plus differential measurements
- Compact sensor head with fixed or variable focus
- Eye-safe, visible, low-power laser probe
- Ruggedized industrial IP-64 housing
- Compatible with AK-800 Beam Steering Unit for difficult-to-access locations
- Large displacement impact testing from a safe operating distance

Applications

Combustion Engine Development


The gas exchange cycle is extremely important for combustion engine development because of its influence on the mixture formation and combustion processes. Valve train performance (kinematics and dynamics) is intimately associated with this cycle and offers considerable opportunity for increasing engine performance. The HSV-2002 is a unique tool that significantly contributes to advanced valve train engineering by allowing for independent measurements of both valve lift and velocity. Displacement and velocity up to 160 mm and 30 m/s, respectively, may be measured. This is important for detecting high frequency bouncing effects.

Both results and resolution are independent of distance, material properties and temperature. The sensor is installed in a safe distance avoiding temperature and oil pollution problems. Using the HSV 2002, development engineers can now optimize valve train parameters early in the product development cycle.

For more information see the application note VIB-C-03 "Measurement of Valve Train Dynamics" which can be downloaded from www.polytec.com/usa/Lm-download.

Fatigue Testing of Turbine Blades

If continuous amplitude and resonance frequency monitoring of test structures (e.g. turbine blades) is required, HSV is the choice. In fatigue testing setups, where structures are excited in their resonance frequencies, HSV enables long term measurements of high amplitudes without contact from a safe distance. Precise and reliable data on durability and the cycles until the development of first cracks allow the verification of numerical predictions.





The HSV was designed for the investigation of high speed processes like

- High speed machinery kinematics
- High speed engine valve dynamics
- Ultrasonic welding
- Explosion, shock impact, door slam and other transient high speed events

High Speed Measurements Through a Microscope on Bubble Jet Drops

For bubble jet printers the ink drop velocities can be as high as 30 m/s. Only the HSV High Speed Vibrometer is capable to deal with such high speeds. The HSV can be combined with a microscope adapter via the CLV-A-Micro adaptor piece. The measurements are made on the bubble jet drops when leaving the printer head capillaries.



Technical Data

Metrological Properties		
	Velocity	Displacement
Frequency range	0... 50 kHz	0... 250 kHz (small signal)
Output swing	± 6 V	± 8 V
Scaling factor	5 m/s/V	0.32; 0.64; 1.28; 2.56; 5.12; 10.24 [mm/V]
Full scale	± 30 m/s	5.12; 10.24; 20.48; 40.96; 81.92; 163.84* [mm p-p]
Resolution	< 15 µm/s**	0.32; 0.64; 1.28; 2.56; 5.12; 10.24 [µm] ***
Max. acceleration	1,000,000 g	45,000,000 g****

* VibSoft-FC extends the maximum range to virtually unlimited

** The noise-limited resolution is defined as the signal amplitude (rms) at which the signal-to-noise ratio is 0 dB in a 10 Hz spectral bandwidth (BW), measured at 3M Scotchlite Tape® (reflective film).

*** The resolution is defined as 1 increment of the fringe counter output, which is equivalent to a 1 mV output voltage step.

**** at 10.24 mm/V, with the tracking filter switched off.

HSV Output Channels		
	HSV-2001 Single Channel	HSV-2002 Dual Channel
Velocity output	Channel A	Channel A, Channel B Channel A - Channel B (differential)
Displacement output	Channel B	Channel A, Channel A – Channel B (differential)

Optics	
Laser output power	< 1 mW (eye safe class 2)
Stand-off distance	<ul style="list-style-type: none"> ■ Variable focus (HSV-700-vf): 0.11 ... 10 m (depending upon surface scattering properties) ■ Fixed focus (HSV-700-ff): 520 mm

Housing and Operational Conditions			
System component	HSV-2001/2002 Controller	HSV-800 Laser Unit*	HSV-700-xx Sensor Head
Dimensions [L x W x H]	450 x 355 x 135 mm (17.7 x 14.0 x 5.3 in) (19")	340 x 130 x 115 mm (13.4 x 5.1 x 4.5 in)	174 x 48 x 39 mm (6.9 x 1.9 x 1.2 in) (ff version)
Weight	8 kg (17.6 lb)	6 kg (13.2 lb)	0.5 kg (1.1 lb)
Protection class	I (protective ground)	IP 64	IP 64
Operating temperature	+5 °C ... +40 °C (41 °F ... 104 °F)		
Storage temperature	-10°C ... +65 °C (14 °F ... 149 °F)		
Relative humidity	max. 80%, non-condensing		
Connection cables	Sensor Head to Laser Unit: standard 3 m (9.8 ft) Laser Unit to Controller: standard 5 m (16.4 ft), optional up to 10 m (32.8 ft)		
Mains voltage	100 ... 240 VAC ± 10 %, 50/60 Hz		
Power consumption	max. 100 VA		

Compliance with Standards	
Electrical safety	IEC/EN 61010-1
EMC	IEC/EN 61326 Emission: FCC Class A, IEC/EN 61000-3-2 and 61000-3-3 Immunity: IEC/EN 61000-4-2 to 61000-4-6 and IEC/EN 61000-4-11
Laser safety	IEC/EN 60825-1 (CFR 1040.10, CFR 1040.11)

For differential operation with using the HSV-2002, two laser units are required.