


DD-200 *Displacement Decoder*



MODULAR VIBROMETER SYSTEM

- OFV-5000
Vibrometer Controller
– Velocity Decoders
– Displacement Decoders
- OFV-505/503
Standard Sensors
- OFV-511/512
Fiber-Optic Sensors

MEASURING VIBRATION DISPLACEMENT

Signal processing is one of the most sensitive parts of any Laser Doppler Vibrometer system. The quality of dedicated displacement decoders available for the OFV-5000 Controller defines the accuracy, linearity, sensitivity and signal-to-noise ratio of the system.

Displacement Decoding in Laser Vibrometer Systems

Polytec Laser Vibrometers measure the instantaneous velocity and displacement of a vibrating test structure from the Doppler shift in the frequency of back-scattered laser light.

A vibrometer system comprises controller electronics and a non-contact standard-optic or fiber-optic sensor head. The controller provides signals and power for the sensor head, and processes the vibration signals. Specially developed decoders electronically convert the raw vibration signal to obtain velocity and displacement information about the test structure.

An OFV-5000 based vibrometer system can measure vibration frequencies from 0 Hz up to 20 MHz and displacements from picometers to meters. Different measurement ranges demand appropriate decoders. To meet this demand Polytec offers a range of displacement decoders with different characteristics.

The DD-200 High-Resolution Displacement Decoder

The DD-200 is designed to measure translational displacement and vibration amplitudes in applications demanding a very high resolution. A total of 13 measurement ranges with resolutions from 2 nm to 10 μm supports the adaptation to most measurement tasks within the frequency range 0 – 250 kHz.

The operating principle is based on an incremental method called fringe counting. An interferometric fringe corresponds to a certain surface displacement. The number of fringes is counted and transformed to an analog output voltage utilizing a digital-to-analog converter.

Key Features of the DD-200

- Digital fringe counting
- 13 measurement ranges with a dynamic range of 14 bit each (> 80 dB)
- Best resolution 2 nm
- Frequency range from DC to 250 kHz



DD-200 Technical Data

Measurement Range	Full Scale Output (Peak to Peak)*	Resolution**	Signal Frequency Range	Max. Velocity
mm/V	mm	μm	kHz	m/s
0.002	0.032	0.002	0 – 25	0.05
0.004	0.064	0.004	0 – 50	0.10
0.008	0.128	0.008	0 – 75	0.20
0.016	0.256	0.016	0 – 75	0.50
0.032	0.512	0.032	0 – 75	1.00
0.080	1.280	0.080	0 – 250	2.50
0.160	2.560	0.160	0 – 250	5.00
0.320	5.120	0.320	0 – 250	10.0
0.640	10.240	0.640	0 – 250	10.0
1.280	20.480	1.280	0 – 250	10.0
2.560	40.960	2.560	0 – 250	10.0
5.120	81.920	5.120	0 – 250	10.0
10.240	163.840	10.240	0 – 250	10.0

* The full scale values correspond to the maximum output voltage swing of ± 8 V.

** The resolution is understood as 1 digit of the fringe counter output or 1 mV at the analog output, resp.

DD-200 Range Diagrams



Data Acquisition

For PC-based data acquisition and processing we recommend our VibSoft Packages. VibSoft-FC is a comprehensive software best suited for the DD-200 decoder for acquiring the vibrometer digital fringe count output signal. It features data acquisition in time and frequency domain, digital filters, signal averaging and real-time integration and differentiation.

For more information on selection and combination of signal decoders please see OFV-5000 and Decoder Guide data sheets, or contact your local vibrometer sales/application engineer.

Polytec GmbH

Polytec-Platz 1-7
76337 Waldbronn
Germany
Tel. + 49 (0) 7243 604-0
Fax + 49 (0) 7243 69944
info@polytec.de

Polytec-PI, S.A. (France)

32 rue Délizy
93694 Pantin
Tel. + 33 (0) 1 48 10 39 34
Fax + 33 (0) 1 48 10 09 66
info@polytec-pi.fr

Lambda Photometrics Ltd. (Great Britain)

Lambda House, Batford Mill
Harpenden, Herts AL5 5BZ
Tel. + 44 (0) 1582 764334
Fax + 44 (0) 1582 712084
info@lambdaphoto.co.uk

Polytec KK (Japan)

Hakusan High Tech Park
1-18-2 Hakusan, Midori-ku
Yokohama-shi, 226-0006
Kanagawa-ken
Tel. +81 (0) 45 938-4960
Fax +81 (0) 45 938-4961
info@polytec.co.jp

Polytec, Inc. (USA)

North American Headquarters
1342 Bell Avenue, Suite 3-A
Tustin, CA 92780
Tel. +1 714 850 1835
Fax +1 714 850 1831
info@polytec.com

Midwest Office

3915 Research Park Dr.,
#A12
Ann Arbor, MI 48108
Tel. +1 734 662 4900
Fax +1 734 662 4451

East Coast Office

25 South Street, Suite A
Hopkinton, MA 01748
Tel. +1 508 544 1224
Fax +1 508 544 1225