

# PSV-400 Scanning Vibrometer



## POLYTEC SCANNING VIBROMETER

- PSV-400 Scanning Vibrometer
- PSV-400-3D Scanning Vibrometer
- MSV-400 Microscope Scanning Vibrometer
- PMA-400 Planar Motion Analyzer
- MMA-400 Micro Motion Analyzer

## SCANNING & VISUALIZING VIBRATIONS

*The completely redesigned PSV-400 Scanning Vibrometer represents state-of-the-art measurement technology for the analysis of structural vibrations. Entire surfaces are rapidly scanned and automatically probed with flexible and interactively created scan grids. The PSV-400 offers technical excellence, ease of use and features designed for resolving noise and vibration issues in the automotive, aerospace, commercial manufacturing and R&D markets.*

### Key Features of the PSV-400

- Easy and intuitive operation and rapid, non-contact vibration measurement
- Digital data decoding available (depending on system configuration)
- Measuring on imported object geometries or on interactively created scan grids
- Focus position of each sample point can be individually set
- Mountable rangefinder (optional) allows acquisition of geometry data
- MIMO (Principal Component Analysis)
- User-defined datasets enable extended and user-defined evaluation procedures
- Incorporates proven OFV-5000 Vibrometer Controller and OFV-505 Sensor Head technology
- Fully upgradeable to the PSV-400-3D 3D measuring Scanning Vibrometer

### Measuring Vibrations of Complete Surfaces

Polytec Laser Doppler Vibrometers are used to precisely measure mechanical vibrations, quickly, easily and free from cross-talk or feedback problems. A modular design allows task specific optimization while retaining maximum flexibility and expandability for future needs.

Polytec Vibrometers operate on the Doppler principle, measuring the frequency shift of back-scattered laser light from a vibrating structure to determine its instantaneous velocity and displacement.

The PSV-400 Scanning Vibrometer is a single, automated, turnkey system that offers all the advantages of a laser vibrometer integrated with the speed, ease of use, accuracy and comprehensive data processing and visualization of a dual-axis laser scanner.

**CAUTION**

LASER RADIATION – DO NOT STARE INTO BEAM



Helium Neon Laser  
1 milliwatt max/cw  
CLASS II LASER PRODUCT

Users get a quick, easily understood and accurate visualization of a structure's global and local vibrational characteristics. The PSV-400 avoids the necessity of attaching a transducer array to the test sample and then individually collecting and processing each transducer's output.

The PSV-400 Scanning Vibrometer comprises both state-of-the-art hardware and software. It includes a compact sensor head with an integrated scanning unit, a vibrometer controller and a data acquisition and management system. These components are complimented by a powerful software package that controls the scanners, data processing, and visualization of the measurement results.

The PSV-400 series is built upon the combined strength of a proven OFV-5000 Controller and a high-performance OFV-505 Sensor Head featuring auto-focus and focus memory functionality.

The PSV-400 is designed to scan both small (mm<sup>2</sup>) and large (m<sup>2</sup>) structures. Depending on the chosen configuration, the PSV-400 covers vibration frequencies up to 20 MHz and vibration velocities up to 20 m/s.

The PSV-400 can be upgraded to the fully featured, 3-dimensional PSV-400-3D Scanning Vibrometer. It is also the base for the award-winning Polytec Microscanning Systems.

## PSV-400 Technical Data

General Specifications	
Working distance	> 0.4 m (shorter distances accessible by using close-up unit*)
Laser wavelength	633 nm, visible beam
Laser protection class	Class II He-Ne laser, < 1 mW, eye-safe
Sample size	Several mm <sup>2</sup> up to m <sup>2</sup> range
Scan grid	Multiple grid densities and coordinate systems (polar, cartesian and hexagonal) each with up to 512 x 512 points combined in one scan

Configurations		
PSV-400-B	Basic Scanning Vibrometer	2 channels, 40 kHz, 10 m/s
PSV-400-H4	High End Scanning Vibrometer	4 channels, 80 KHz, 10 m/s
PSV-400-H4-S	High Amplitude Scanning Vibrometer	4 channels, 80 KHz, 20 m/s*
PSV-400-M2	Wide Bandwidth Dual Channel Scanning Vibrometer	2 channels, 1 MHz, 10 m/s
PSV-400-M4	Wide Bandwidth Four Channel Scanning Vibrometer	4 channels, 1 MHz, 10 m/s
PSV-400-M2-20	20 MHz Scanning Vibrometer	2 channels, 20 MHz, 10 m/s*

\* available 2004

PSV-400 Hardware	
Sensor Head PSV-I-400	<p>Components:</p> <ul style="list-style-type: none"> <li>- High sensitivity vibrometer sensor model OFV-505</li> <li>- High precision scan unit (scanning range <math>\pm 20^\circ</math> about X, Y) Angular resolution <math>&lt; 0.002^\circ</math>, angular stability <math>&lt; 0.01^\circ</math> /hr</li> <li>- Color video camera with Auto Focus and 72x Zoom (4x digital, 18x optical)</li> </ul> <p>Features:</p> <ul style="list-style-type: none"> <li>- Scan speed <math>&gt; 100</math> points/s</li> <li>- Individual focusing of each scan point utilizing remote focus control with memory position function</li> <li>- Mountable rangefinder for acquisition of test sample geometry (optional)*</li> <li>- Working distance <math>&gt; 0.4</math> m (standard)</li> <li>- Weight 7.5 kg</li> <li>- Dimensions (L x H x W) 365 mm x 160 mm x 190 mm</li> </ul>
Vibrometer Controller OFV-5000	<ul style="list-style-type: none"> <li>- Velocity ranges: 2/10/50/100/1000 [mm/s/V] (PSV-400-B: 10/100/1000 [mm/s/V]; (PSV-400-M2-20: 5/25/125/1000 [mm/s/V]; further ranges dependent on the decoder configuration)</li> <li>- Bandwidth: 1.5 MHz (PSV-400-M2-20: 20 MHz)</li> <li>- Four analog low pass filters with limit frequency 5 kHz, 20 kHz, 100 kHz and 1.5 MHz resp.</li> <li>- RS 232 interface for remote control by the Data Management System</li> </ul>
Junction Box PSV-E-400	<p>Interface between PSV-I-400 Sensor Head, OFV-5000 Vibrometer Controller and the Data Management System</p> <ul style="list-style-type: none"> <li>- Input for 4 analog signals, triggers and gate available on BNC connectors, ICP-compatible</li> <li>- Output for signal generator available on BNC connectors</li> </ul>
Data Management System PSV-W-400	<p>State-of-the-art rack-mountable industrial PC equipped with:</p> <ul style="list-style-type: none"> <li>- DVD-Recorder</li> <li>- 17" LCD Display</li> <li>- 100 MB Ethernet network connection</li> <li>- Data acquisition: <ul style="list-style-type: none"> <li>PSV-400-B 2 channels, 40 kHz bandwidth</li> <li>PSV-400-H4 4 channels, 80 kHz bandwidth</li> <li>PSV-400-H4-S 4 channels, 80 kHz bandwidth</li> <li>PSV-400-M2 2 channels, 1 MHz bandwidth</li> <li>PSV-400-M4 4 channels, 1 MHz bandwidth</li> <li>PSV-400-M2-20 2 channels, 20 MHz bandwidth</li> </ul> </li> <li>- Signal generator</li> <li>- Operating system Windows® 2000 or Windows® XP (German, English and Japanese version available)</li> </ul>
Systems cabinet, rollable (optional)	Houses PC Workstation, Vibrometer Controller, Junction Box and Data Management System
Motorized pan/tilt head (optional)	Maximum panning angle (horizontal): $\pm 90^\circ$ , Maximum tilt angle (vertical): $\pm 84^\circ$

\* available 2004

PSV-400 Software Features	
2D Alignment	- Simple and interactive procedure to align the coordinates of the video image to the coordinates of the scanners
Scan grid definition	Two alternatives: <ul style="list-style-type: none"> <li>- Manual, interactive definition in the live video image by APS Professional (Advanced Point Selection), allows multiple grid densities and coordinate systems (polar, cartesian and hexagonal) each with up to 512 x 512 points combined in one scan</li> <li>- Data import from CAD- and FEM-systems via Universal File Format (UFF) or ASCII or binary from MEscape (optional)</li> </ul>
Focus control	- Focus Scan and Focus Memory used to determine and save the optimum focus position of each respective scan point
Data acquisition	<ul style="list-style-type: none"> <li>- Simultaneous data acquisition from up to 4 channels (vibrometer signal, 3 reference signals)</li> <li>- Acquisition modes: FFT; zoom-FFT (optional available except for B); fast scan (optional for B); multi frame (optional, only for H); time mode (optional)</li> <li>- Digital filtering and averaging available</li> <li>- Trigger options: external, analog, pre and post trigger</li> </ul>
Data quality	Continuous assessment of the S/N ratio in order to improve data quality by Signal Enhancement (increased number of samples used for averaging) and Speckle Tracking
Target data	<ul style="list-style-type: none"> <li>- Velocity is measured; displacement (calculated by integration of velocity) and acceleration (calculated by differentiation) can also be displayed</li> <li>- Data are saved in form of either spectra or time signal (optional for scan data)</li> <li>- Calculation of transfer functions between primary and reference signals: FRF, H1, H2, Coherence, Autopower, Crosspower</li> </ul>
Data presentation	<p>Spectral presentation:</p> <ul style="list-style-type: none"> <li>- Spectrum averaged over all scan points</li> <li>- Spectra of individual points</li> </ul> <p>Display of video image overlaid with measured data and various presentation modes of deflection shapes:</p> <ul style="list-style-type: none"> <li>- 2D: color map presentation of vibration data</li> <li>- 3D: 3-dimensional presentation of vibration data</li> <li>- Isolines: equivalent values are interconnected by colored isolines</li> <li>- Scan point: Each scan point is depicted as a square symbol colored according to the measured value</li> </ul> <p>Profile representation of section cuts across the test sample which are created interactively</p>
Data export	<ul style="list-style-type: none"> <li>- Windows® Automation Interface: Polytec FileAccess (enables data access utilizing Visual Basic or C++)</li> <li>- Export of geometry data, spectra, time signals and deflection shapes as UFF- and ASCII-file (Excel format), optional</li> <li>- Export of animated 2D- and 3D-models and profiles as AVI-file</li> </ul>
Signal generation	The internal signal generator is used to create specific excitation signals

**Polytec GmbH**  
 Polytec-Platz 1-7  
 76337 Waldbronn  
 Germany  
 Tel. + 49 (0) 7243 604-0  
 Fax + 49 (0) 7243 69944  
 info@polytec.de

**Polytec-PI, S.A.**  
 32, rue Délizy  
 93694 Pantin  
 France  
 Tel. +33 (0)148 10 39 30  
 Fax +33 (0)148 10 08 03  
 info@polytec-pi.fr

**Lambda Photometrics Ltd.**  
 Lambda House, Batford Mill  
 Harpenden, Herts AL5 5BZ  
 Great Britain  
 Tel. + 44 (0)1582 764334  
 Fax + 44 (0)1582 712084  
 info@lambdaphoto.co.uk

**PI-Polytec K.K.**  
 Akebono-cho 2-38-5  
 Tachikawa-shi  
 Tokyo, 190-0012  
 Japan  
 Tel. + 81(0) 42 526-7300  
 Fax + 81(0) 42 526-7301  
 info@pi-polytec.co.jp

**PI-Polytec K.K.**  
 4-11-27 Nishihakashima  
 Yodogawa-ku,  
 Osaka-shi, Osaka-fu  
 Japan  
 Tel. +81(0) 6 6304-5605  
 Fax +81(0) 6 6304-5606

**Polytec-PI, Inc.**  
 East Coast Office  
 16 Albert Street  
 Auburn, MA 01501  
 USA  
 Tel. +1 508 832 3456  
 Fax +1 508 832 0506  
 info@polytepci.com

**Polytec-PI, Inc.**  
 West Coast Office  
 1342 Bell Avenue, Suite 3-A  
 Tustin, CA 92780  
 USA  
 Tel. + 1 714 850 1835  
 Fax + 1 714 850 1831